



HBA - Perfect for "Industrial" retail

HBA Low Bay

The HBA is a high efficiency luminaire for general purpose and retail lighting. This luminaire is ideal for retail stores, warehouse aisles, and industrial applications where uplight is required.

Benefits

- Heavy duty construction
- Cooler operation for longer life
- Provides uplight

Features

- Two piece die cast aluminum housing
- Day-Brite "Slant 2" ballast mounting
- Injection molded acrylic reflector

Application

- Retail
- Manufacturing
- Industrial

HBA Low Bay

Versions

