



# HBE - Traditional and efficient

## HBE Enclosed High Bay Acrylic Reflector

The HBE400 Enclosed High Bay Luminaire features an enclosed, acrylic reflector for maximum efficiency in general purpose retail, educational and industrial applications requiring uplight and enclosed construction.

### Benefits

- Heavy duty construction
- Cooler operation for longer life
- Field adjustable light distribution
- Provides uplight

### Features

- Two piece die cast aluminum housing
- Day-Brite "Slant 2" ballast mounting
- Die cast neck with adjustable socket location
- Injection molded acrylic reflector

### Application

- Manufacturing
- Industrial
- Warehouse

## HBE Enclosed High Bay Acrylic Reflector

### Versions

