



HBE - Traditional and efficient

HBE Enclosed High Bay Aluminum Reflector

The HBE Enclosed High Bay Luminaire features enclosed, spun aluminum reflector with a clear tempered glass lens for use in applications requiring dust tight or wet location (optional) construction.

Benefits

- Heavy duty construction
- Cooler operation for longer life
- Field adjustable light distribution

Features

- Two piece die cast aluminum housing
- Day-Brite "Slant 2" ballast mounting
- Die cast neck with adjustable socket location
- Precision spun aluminum reflector

Application

- Manufacturing
- Industrial
- Warehouse

HBE Enclosed High Bay Aluminum Reflector

Versions

