



# HBO - Traditional and efficient

## HBO Open High Bay Acrylic Reflector

The HBO Open High Bay Luminaire features an open, acrylic reflector for maximum efficiency in general purpose retail, educational and industrial applications where upright is required.

### Benefits

- Heavy duty construction
- Cooler operation for longer life
- Field adjustable light distribution
- Provides upright

### Features

- Two piece die cast aluminum housing
- Day-Brite "Slant 2" ballast mounting
- Heavy gauge adjustable yoke for reflector mounting
- Injection molded acrylic reflector

### Application

- Manufacturing
- Industrial
- Warehouse

## HBO Open High Bay Acrylic Reflector

### Versions

