



HBO - Traditional and efficient

HBO Open High Bay Aluminum Reflector

The HBO Open High Bay Luminaire features open spun aluminum reflectors for maximum efficiency in general purpose retail, educational and industrial applications.

Benefits

- Heavy duty construction
- Cooler operation for longer life
- Field adjustable light distribution
- Provides uplight

Features

- Two piece die cast aluminum housing
- Day-Brite "Slant 2" ballast mounting
- Heavy gauge adjustable yoke for reflector mounting
- Precision spun aluminum reflector

Application

- Manufacturing
- Industrial
- Warehouse

HBO Open High Bay Aluminum Reflector

Versions

