



# HCE - Traditional and efficient

## HCE Enclosed High Bay Acrylic Reflector

The HCE Enclosed High Bay Luminaire features an enclosed, acrylic reflector for maximum efficiency in general purpose retail, educational and industrial general purpose retail, educational and industrial construction.

### Benefits

- Heavy duty construction
- Field adjustable light distribution
- Provides uplight

### Features

- Two piece die cast aluminum housing
- Die cast neck with adjustable socket location
- Injection molded acrylic reflector

### Application

- Manufacturing
- Industrial
- Warehouse

## HCE Enclosed High Bay Acrylic Reflector

### Versions

