



HCE - Traditional and efficient

HCE Enclosed High Bay Aluminum Reflector

The HCE Enclosed High Bay Luminaire features an enclosed, aluminum reflector for maximum efficiency in general purpose retail, educational and industrial general purpose retail, educational and industrial construction.

Benefits

- Heavy duty construction
- Field adjustable light distribution

Features

- Two piece die cast aluminum housing
- Die cast neck with adjustable socket location
- Precision spun aluminum reflector

Application

- Manufacturing
- Industrial
- Warehouse

HCE Enclosed High Bay Aluminum Reflector

Versions

