



# HCF - Flexible lighting with traditional style

## HCF Open High Bay Acrylic Reflector

The HCF Compact Fluorescent luminaire is an energy saving and efficient light source. Standard features include: 26, 32, or 42 watt compact fluorescent lamps. Universal voltage 2-lamp electronic ballasts. Locking sockets. Up to four levels of light by switching power to the ballasts. Dimming ballast options for up to 8 lamps (0-10V Advance Mark VII standard). Emergency ballast optional.

### Benefits

- Heavy duty construction
- Multi-level switching capability
- Secure lamp connections
- Provides uplight

### Features

- Die cast aluminum housing
- Multiple compact fluorescent ballasts
- Locking sockets
- Injection molded acrylic reflector

### Application

- Manufacturing
- Retail

## HCF Open High Bay Acrylic Reflector

### Versions

