



# HCO - Traditional and efficient

## HCO Open High Bay Acrylic Reflector

The HCO Open Acrylic Highbay features a heavy gauge yoke that provides positive mounting of the acrylic reflector to the ballast assembly and field adjustable lighting distribution. This luminaire is designed for general purpose, retail, educational and industrial applications.

### Benefits

- Heavy duty construction
- Field adjustable light distribution
- Provides uplight

### Features

- Two piece die cast aluminum housing
- Heavy gauge adjustable yoke for reflector mounting
- Injection molded acrylic reflector

### Application

- Manufacturing
- Industrial
- Warehouse

## HCO Open High Bay Acrylic Reflector

### Versions

