



# Exceeding requirements and meeting today's needs

## HP90 Fluorescent

HP90 Recessed Direct/Indirect: DayBrite's HP90, part of our popular soft light collection of luminaires, specifically addresses today's needs for balance brightness lighting, while exceeding LEED requirements for reducing energy consumption. The HP90 combines a recessed contoured body with an enclosed linear prismatic translucent lens to create an exciting 90.4% efficient direct/indirect luminaire. HP90 is available both in static and Air Supply or Return construction

### Benefits

- Stylish appearance

### Features

- Lamp shields open from either sides

### Application

- Office
- Banks
- Hospitality
- Fashion

## HP90 Fluorescent

### Versions

