



Architectural with customizable energy solutions

HP90 LED

The DayBrite HP90 Recessed LED family is one of our popular soft light collection of luminaires. This is the first introduction of LED with a direct/indirect appearance utilizing highly reflective paint on the soft contoured reflectors and high light transmission linear prismatic lens to enclose the LEDs. HP90 LED family is offered in 1x4, 2x2 and 2x4, giving the customer the ability to truly customize their energy consumption and take control of finding solutions to their own unique lighting level needs.

Benefits

- Can be continuous row mounted

Features

- Same fixture fits both G and T ceiling types
- Only 5" deep
- Suitable for damp locations
- High efficiency LEDs have 50,000 hour rated life at L7

Application

- Office
- Hospitality
- Education

HP90 LED

Versions

