



# i15 Inground - durable and discreet illumination

## i15 Inground

The revolutionary i1.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench - the i1.5 reinforces HADCO's position as the leader in landscape lighting.

### Benefits

- Ensures long-lasting durability
- Creates a variety of effects
- Up to 50,000 hour life with LED module
- High-impact resistance
- Dust-tight, dual-rated, sealed against direct jets of water and continuous immersion

### Features

- Single-piece composite housing includes separate sealed compartments
- Available with a variety of light sources, including LED lamps and modules
- Tempered borosilicate lens
- IP66/68 rated

### Application

- Landscape

Accessories



Ordercode I15CRGN



Ordercode I15CRGSS



Ordercode I15FRL



Ordercode I15HDN



Ordercode I15HDSS



Ordercode I15SRL



Ordercode CPS15

