



i2 Inground - durable and discreet illumination

i2 Inground

The i2 Inground is a line voltage in-ground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

Benefits

- Design flexibility
- Up to 30,000 hour life with LED
- Ensures long-lasting durability
- Prevents water leaks
- Glare control

Features

- Available with conventional and LED technology
- Offers several color temperatures
- Single-piece composite housing
- Rock guard available
- IP67 rated

Application

- Landscape

i2 Inground

Versions



Accessories



Ordercode CP2



Ordercode CPS2

