



# iUL516 – durable and discreet illumination

## iUL516 Inground

Hadco's iUL516 is a compact low voltage composite landscape luminaire for inground applications. Lamping sources include 35W maximum MR16 bi-pin lamp and LED. Construction includes a one-piece injection molded ULTEM® High Performance Polymer composite body with a single piece injected lens ring and gasketed lens. Twist-off operation for ease of maintenance.

### Benefits

- Design flexibility
- Up to 25,000 hour life with LED
- Ensures long-lasting durability
- Provides added corrosion resistance
- Quick and easy installation

### Features

- Available with conventional and LED technology
- ULTEM composite housing
- Color impregnated material finish
- Pre-wired

### Application

- Landscape

## iUL516 Inground

### Versions

