



# Kleenseal 100 - Superior and practical

## Kleenseal 100 Recessed Cleanroom

The Kleenseal KTR 100 is a cleanroom luminaire well suited for laboratories, fuel storage areas and dirty areas such as locker rooms. Ideal for Class 100-100,000 cleanrooms.

### Benefits

- Designed to resist corrosion
- Lightweight
- Speedy installation

### Features

- Suitable for wet locations
- Sealed aluminum housing
- Seismic support mounting is standard
- Class 100-100,000 cleanrooms

### Application

- Cleanrooms
- Food Processing

## Kleenseal 100 Recessed Cleanroom

### Versions

