



Kleenseal 200 – Superior and practical

Kleenseal 200 Recessed Cleanroom

Kleenseal KTR 200 is a hosedown cleanroom luminaire well suited for laboratories, food processing areas, waste water facilities and chemical plants. It can withstand 200 psi hosedown and is NSF listed.

Benefits

- Designed to resist corrosion

Features

- Suitable for wet locations
- Sealed aluminum housing with steel optional
- Seismic support mounting is standard

Application

- Cleanrooms
- Food Processing

Versions

