



Kleenseal 50 - Superior and practical

Kleenseal 50 Recessed Cleanroom

Kleenseal KTR 50 is a cleanroom luminaire suited for laboratories, fuel storage areas and dirty areas such as locker rooms.

Benefits

- Designed to resist corrosion
- Lightweight
- Speedy installation
- Easy tool-free access

Features

- Suitable for wet locations
- Sealed aluminum housing
- Door is hinged to housing

Application

- Cleanrooms
- Food Processing

Kleenseal 50 Recessed Cleanroom

Versions

