



# L40U - blending traditional luminaire forms with modern lighting function

## L40U LED pendant (L40U-STM)

The L40U luminaires feature a one-piece square tapered cast aluminum housing, with a sealed optical system. The cast-aluminum hood includes a photoelectrical hiding decorative finial, assembled on the housing using two built-in hood hinges. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php) target="\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

### Benefits

- Protected against moisture, dust and insects
- Quick and easy maintenance
- Suitable for a variety of applications

### Features

- IP66 rated optical system
- Toolless access to internal components
- Various optics available

### Application

- Road and Street

## L40U LED pendant (L40U-STM)

### Versions

