



# LLB - Quality and high efficiency

## LLB Low Bay

The LLB Luminaire provides the industry's highest efficiency for general purpose industrial lighting. A geometrically balanced fixture, this small luminaire can be mounted within 6' of the working surface.

### Benefits

- Easy, positive mounting
- Latches designed to resist corrosion

### Features

- Suitable for wet locations
- 3/4" threaded cast aluminum nut and hub
- Heavy wall, one piece die cast aluminum housing
- Stainless steel latches
- One piece injection molded lens

### Application

- Manufacturing
- Industrial

## LLB Low Bay

### Versions

