



# Low Bay 400 - Quality and high efficiency

## Low Bay 400

The Low Bay 400 is a high efficiency low bay luminaire designed for use in general purpose retail, educational and industrial applications.

### Benefits

- Easy, positive mounting
- Ease of maintenance

### Features

- Suitable for damp locations
- 3/4" threaded cast aluminum nut and hub
- Heavy wall, two piece die cast aluminum housing
- One piece injection molded lens

### Application

- Manufacturing
- Industrial

## Low Bay 400

### Versions

