



# LP20 - combining elegance with state-of-the-art photometrics

## LP Post Top (LP20)

Combining elegance with state-of-the-art photometrics, the LP20 luminaire has been designed to harmonize beautifully with park and urban settings. This unit consists of a clear satin, one-piece, injection-molded globe mechanically assembled on a quarter-turn access mechanism. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php) target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Quick and easy maintenance
- Protects against water
- Shock-resistant
- Fade, abrasion, and UV resistant

### Features

- Tool-free access to internal components
- Injected clear satin polycarbonate globe
- Silicone gasketing
- Polyester powdercoat finish

### Application

- Road and Street
- Bridges, Monuments, Facades