



# The contractor

## Lytening Frames

For the fastest, most convenient installation in insulated ceiling residential construction. Accommodates new ceilings up to 2" thick. "Swivelock" pivoting mounting bars permit installation and wiring below the ceiling. Pre-installed nails or screws. Complies with Air Leakage Requirements stated in the Model Energy Code and the Washington State Energy Code

### Benefits

- Design allows below ceiling wiring for quick install
- Bar design minimizes flex

### Features

- Pivoting bar ends allow convenient wiring below the ceiling and fast installation

### Application

- Office
- Banks
- Hospitality
- Airports
- Fashion

## Lytening Frames

### Versions

