



# Style and versatility

## LytePoints Line Voltage 4 1/4"

Designing with light means creating the right atmosphere for the decor. Use this brochure to select the right lighting tool for the lighting effect you want to achieve. Quickly identify the most appropriate 500X Series luminaire for your lighting needs by

### Benefits

- Comprised of a complete palette of interchangeable trim choices
- Designed around the "Flex" system for a contractor friendly installation
- Each luminaire is designed with a combination of high performance and unparalleled aesthetics

### Features

- Transformer is mounted vertically to dramatically reduce noise
- Frame options for MR16 or ES16 lamps
- Factory installed trim enclose simplifies installation
- Open downlight, wall wash, gimbal, slot, pinhole, cross blade trim options available

### Application

- Petrol and Convenience
- Tunnel
- Residential

## LytePoints Line Voltage 4 1/4"

### Versions

