



MetroScape - modern styling meets advanced lighting technology

MetroScape LED Pendant (MSR)

The MetroScape LED Pendant luminaire combines style and performance to create flexible, durable and attractive energy-saving solutions that blend in well with traditional-styled urban architecture. Thanks to the open design it is capable of more powerful lumen packages suited to the higher visibility requirements of roads and intersections – up to 96 LEDs can deliver over 20,000 lumens, equivalent to 400W HID. The pendant model comes with a choice of flat or sag lens, and an optional white opaque globe to accentuate the classic design. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php) target="_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

Benefits

- Optimized LED efficiency and life
- Reduces light pollution, dark-sky friendly
- Ensures durability and reliability in harsh environmental conditions
- Maximizes pole spacings
- Superior light quality and uniformity

Features

- Optimal thermal design includes die cast aluminum heat sink and placement of electronic components in fitter
- Full cutoff with 0% uplight
- Complete luminaire is IP66 rated
- Optical systems composed of high performance refractor lenses
- Dedicated LED optics

MetroScape LED Pendant (MSR)

Application

- Bridges, Monuments, Facades
- Road and Street

