



# MicroSquare gen2 - Highest quality, discreet, narrow lines of continuous light to fit the needs of endless applications.

## MicroSquare gen2 suspended

Ledalite's MicroSquare gen2 has been re-engineered to furnish your space with the highest quality, discreet, narrow lines of continuous light. Elegant, low glare illumination with wide-throw upper and lower distributions improve visual comfort while allowing increased fixture spacing. This in turn, helps reduce initial and operating costs.

### Benefits

- High efficacious illumination
- Sleek new endcap options for contemporary spaces

### Features

- LED light source
- Lower hemisphere utilizes the 2nd generation of Ledalite's 'Silk' engineered diffuser for higher efficacy and softer appearance.
- New lower Silk lens ensures a smooth gradation of light down the vertical surface.
- New selection of endcaps

## MicroSquare gen2 suspended

### Application

- Office
- Education
- Hospitality
- Fashion

### Versions

