



# Sleek unobtrusive designs

## Mini HID Accessories

CMH luminaires offer up to 70% energy savings vs. incandescent spotlights with 3 to 4 times longer lamp life. Lytespan Mini HID is the choice for high-performance energy smart retail and architectural lighting.

### Benefits

- Offering up to 70% energy savings vs. incandescent spotlights
- Wide range of beam spreads from narrow (10°) to wide flood (40°)
- Reflectors are available in clear anodized or incandescent warm finish

### Features

- Pivot Mounts: Allows for 350° horizontal and 0-90° vertical rotation with tensioned mounts for controlled aim
- Movable Contact: Solid Brass. Extends for connection to 2nd circuit in Advent track
- Five different lamp types available including 20W miniatures and a full range of PAR lamps
- Available in cylinders and wall washers

### Application

- Fashion
- Food and Large Retailers

## Mini HID Accessories

### Versions



### Accessories



Ordercode 8195

