



# Mini Wallcube LED - classic design, improved LED performance

## Mini Wallcube LED

The Keene 313 LED Wall Pack offers maximum light output for general purpose area and security lighting through a classic glass refractor design. Now available with enhanced Philips LED platforms, WP provides up to 22% more lumens and consumes 46% less energy than the former LED design. This versatile luminaire is ideal to match same as existing or retrofit HID legacy designs.

### Benefits

- Consumes 43% less energy than previous generation
- Increased lumen output
- Fade and abrasion resistant
- Matches existing luminaires or HID retrofits

### Features

- Glass refractor design
- Several controls option available
- One-piece die cast aluminum housing
- TGIC powdercoat finish

### Application

- Security Lighting

## Mini Wallcube LED

### Versions

