



OB361 – elegantly designed for commercial applications

OB361 Bollard

Hadco's OB361 is one of a series of elegant bollards designed for commercial application. This line voltage luminaire is available in incandescent, CFL, HID and LED sources, and is manufactured from high-strength, low-copper, proprietary cast aluminum alloy. Optics include a choice of high performance refractive panels and louvers for a variety of light distributions.

Benefits

- Ensures long-lasting durability and reliability
- Fade and abrasion resistant
- Design flexibility
- Suitable for a variety of applications

Features

- Die cast aluminum housing
- Polyester powdercoat finish
- Available in a variety of lamp technologies
- Variety of optics available

Application

- Bridges, Monuments, Facades
- Landscape

OB361 Bollard

Versions

