



# OB361 LED - elegantly designed for commercial applications

## OB361 Bollard LED

Hadco's OB361 is one of a series of elegant bollards designed for commercial application. This line voltage luminaire is available in incandescent, CFL, HID and LED sources, and is manufactured from high-strength, low-copper, proprietary cast aluminum alloy. Optics include a choice of high performance refractive panels and louvers for a variety of light distributions.

### Benefits

- Ensures long-lasting durability and reliability
- Fade and abrasion resistant
- Offers 50,000 hour life with LED
- Design flexibility
- Suitable for a variety of applications

### Features

- Die cast aluminum housing
- Polyester powdercoat finish
- Warm or cool color temperatures available
- Variety of optics available

### Application

- Bridges, Monuments, Facades
- Landscape

## OB361 Bollard LED

### Versions

