



# OCLM - Aesthetically designed, high efficiency

## OCLM LED Mirror Light

An aesthetically designed high efficiency dressing area fluorescent mirror lighting fixture (mirror not included). The fixture housing is constructed of cold rolled steel that is post painted with a highly durable powder coat making this an excellent choice for areas where some abuse may occur. All seams and joints are kept to very light tolerances, also minimizing chances of abuse. The OCLM fixture is ideal for dressing rooms, fitting areas and anywhere where mirror lighting is needed.

### Benefits

- Creates the excellent light distribution desired in a retail dressing area
- Designed for low glare

### Features

- Comes standard with brackets for wall mounting adjacent to mirror sides
- Housing and wall brackets are brake formed from heavy gauge cold rolled steel
- Curved linear prismatic acrylic diffusers

### Application

- Fashion
- Hospitality
- Office

OCLM LED Mirror Light

Versions

