



Optima - designed to enhance

Optima Post Top (OT10-OT20)

Combining state-of-the-art photometric performance and outstanding ease of maintenance, the Optima is designed to last. The Optima is the perfect choice for landscaped projects that compel that extra little bit of detail. This beautiful luminaire is made from top-quality materials, is easy to maintain, and adds a distinctive decorative aspect to any contemporary environment. Optional LifeLED light engine uses up to 50% less energy and last 3-7 times longer than HID sources. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php" target="_blank"~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)[~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~](#)[~LT~/a~GT~](#)

Benefits

- Up to 50% energy savings over HID
- Virtually eliminates Luminaire Dirt Depreciation
- Reduce glare
- Offers exceptional performance and cut-off
- Dark-sky friendly

Features

- IP66 rated Smartseal optical system
- Unique combination of reflectors and internal prism refractors in optical chamber
- Hydro-formed aluminum reflector and tempered glass lens
- Provide full cut-off in five different distributions

Application

- Road and Street
- Bridges, Monuments, Facades