



Oval - daring to be different

Oval Arm Mount (ECLW)

Recognized for being visually appealing, they are also very technologically advanced. When creativity is focused on details, the details will create ambience. The soft light cast by these discrete luminaires with their refined design makes them an integral part of a finished work. Our wall sconces were designed to complement our lines of luminaires and to add a polished look and feel to any project. ~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php" target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Enhances style of any project
- Maximizes photometric performance and energy efficiency
- Exceptional durability and long life
- Quick and easy maintenance
- Fade and abrasion resistant housing

Features

- Pure and timeless shape
- Smartseal optical systems
- Die-cast aluminum housing
- Tool-free access to internal components
- Polyester powdercoat finish

Application

- Bridges, Monuments, Facades
- Road and Street