



Style, quality and value

PAR Ring

These Lytespots summarize the concept of minimal form and maximum function. They accommodate a full selection of accessories. The result is a range of Lytespots that can perform many lighting tasks in a variety of environments. Cleanly styled yoke offers smart design and attractive style(no cage effect). User friendly: one hand front relamping.

Benefits

- Movable brass contacts extends for connection to 2nd circuit in Advent Lytespan Track

Features

- Designed with minimalistic form to create a close fit with LED lamps
- Units adjust horizontally up to 350° and vertically up to 90°
- Front re-lamping for easy maintenance

Application

- Office
- Banks
- Hospitality
- Residential

PAR Ring

Versions

