



# AM8 - enhancing your project's unique style

## Pole (AM8)

Made from a one-piece, seamless 4" round (102 mm) tube of extruded aluminum welded over and in a 8 5/8" round (219 mm) extruded-aluminum pole base. The assembly is welded to both the top and bottom of a cast aluminum anchor plate. A 4 1/2" by 10" (114 by 254 mm) maintenance opening is complete with cover and copper ground lug. ~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\_en.php" target="\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round
- Aluminum construction
- Available in various heights ranging from 8' to 20'

### Application

- Bridges, Monuments, Facades
- Road and Street

## Pole (AM8)

### Versions

