



# R80A - enhancing your project's unique style

## Pole (R80A)

Made from a 4" round (102 mm) 8 flute extruded-aluminum shaft welded to a decorative cast-aluminum base incorporating an anchor plate. A 4" by 10" (140 by 254 mm) maintenance opening is complete with cover and copper ground lug. The pole comes with cast-aluminum bolt covers. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php" target="\\_blank"~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round fluted
- Aluminum construction
- Available in various heights ranging from 8' to 18'

### Application

- Bridges, Monuments, Facades
- Road and Street

## Pole (R80A)

### Versions

