



# Enhancing your project's unique style

## Traditional Poles (RTA500)

Single-piece 12 flute, mandrel-formed, aluminum tapered shaft 6" round (152 mm) welded top and bottom to a cast-aluminum anchor plate. After tapering, forming and welding, the entire shaft assembly is heat-treated to T6 temper. A 3" by 5" (76 by 127 mm) maintenance opening is complete with aluminum cover and copper ground lug.

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round fluted
- Aluminum construction
- Available in various heights ranging from 12' to 18'

### Application

- Bridges, Monuments, Facades
- Road and Street

## Traditional Poles (RTA500)

### Versions

