



# RS130 - enhancing your project's unique style

## Pole (RS130)

Made from a 16 flute, mandrel-formed tapered steel shaft welded to an 8 5/8" (219 mm) round steel pole base which is then welded to both the top and bottom of a cast aluminum anchor plate. A 4 1/2" by 10" (114 by 254 mm) maintenance opening is complete with a copper ground lug. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php) target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round tapered fluted
- Steel construction
- Available in various heights ranging from 12' to 30'

### Application

- Bridges, Monuments, Facades
- Road and Street

## Pole (RS130)

### Versions

