



# RS804 - enhancing your project's unique style

## Pole (RS804)

Made from a one-piece, 4" round (102 mm) tube of high-tensile carbon steel sealed by a rolled and flattened vertical weld seam and welded to both the top and bottom of a steel anchor plate. A 2" by 4 1/2" (51 by 114 mm) maintenance opening is complete with cover and copper ground lug. [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index\\_en.php"](http://www.lumec.com/Lumec3Dv2/home/index_en.php) target="\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round
- Steel construction
- Available in various heights ranging from 8' to 20'

### Application

- Bridges, Monuments, Facades
- Road and Street

## Pole (RS804)

### Versions

