



RS805 - enhancing your project's unique style

Pole (RS805)

Made from a one-piece, 5" round (127 mm) tube of high-tensile carbon steel sealed by a rolled and flattened vertical weld seam and welded to both the top and bottom of a steel anchor plate. A 2" by 4 1/2" (51 by 114 mm) maintenance opening is complete with cover and copper ground lug. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php" target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)

Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

Features

- Round
- Steel construction
- Available in various heights ranging from 14' to 30'

Application

- Bridges, Monuments, Facades
- Road and Street

Pole (RS805)

Versions

