



RTA800 - enhancing your project's unique style

Pole (RTA800)

Made from tapered 6" to 4" (152 to 102 mm) round aluminum shaft welded to a cast-aluminum anchor plate. After tapering and welding, the entire shaft assembly is heat-treated to T6 temper. A 3" by 5" (76 by 127 mm) maintenance opening is complete with cover and copper ground lug. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php" target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)

Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

Features

- Round tapered fluted
- Aluminum construction
- Available in various heights ranging from 8' to 20'

Application

- Bridges, Monuments, Facades
- Road and Street

Pole (RTA800)

Versions

