



# RTAF800 - enhancing your project's unique style

## Pole (RTAF800)

Made from a 12 flute, mandrel-formed aluminum tapered shaft, welded top and bottom to a cast-aluminum anchor plate. After tapering and welding, the entire shaft assembly is heat-treated to T6 temper. A 3" by 5" (76 by 127 mm) maintenance opening is complete with cover and copper ground lug. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php" target="\\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round tapered fluted
- Aluminum construction
- Available in various heights ranging from 12' to 18'

### Application

- Bridges, Monuments, Facades
- Road and Street

## Pole (RTAF800)

### Versions

