



# SSM8 - enhancing your project's unique style

## Pole (SSM8)

Made from a one-piece, seamless 5 9/16" round (141 mm) high-tensile carbon steel shaft sealed by a rolled and flattened vertical weld seam and welded over and in a 8 5/8" round (219 mm) high-tensile carbon-steel pole base. The assembly is welded to both the top and bottom of a steel anchor plate. A 4 1/2" by 10" (114 by 254 mm) maintenance opening is complete with cover and copper ground lug. [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index\\_en.php"](http://www.lumec.com/Lumec3Dv2/home/index_en.php) target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round
- Steel construction
- Available in various heights ranging from 18' to 28'

### Application

- Bridges, Monuments, Facades
- Road and Street

## Pole (SSM8)

### Versions

