



# RTA126/RTA127 - enhancing your project's unique style

## Poles (RTA126/RTA127)

Made from tapered 6" to 4" (152 to 102 mm) & 7" to 4" (178 to 102 mm) round aluminum shaft welded to a 6 5/8" round (168 mm) extruded aluminum pole base which is welded top and bottom to a cast-aluminum anchor plate. After tapering and welding, the entire shaft assembly is heat-treated to T6 temper. A 4 1/2" by 10" (114 by 254 mm) maintenance opening is complete with cover and copper ground lug. [~LT~br~GT~ ~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php" target="\\_blank"~GT~ ~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~ ~LT~/a~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)

### Benefits

- Built to withstand harsh environmental conditions
- Superior corrosion resistance
- Optimal strength and durability

### Features

- Round tapered
- Aluminum construction
- Available in various heights ranging from 10' to 20'

### Application

- Road and Street
- Bridges, Monuments, Facades

## Poles (RTA126/RTA127)

### Versions

