



# Dramatic light, high efficiency

## PowerWash Track Heads

PowerWash T5 Track Mount represents the state of the art in Energy Smart linear fluorescent wall washing and flood lighting combined with the unsurpassed flexibility of Lytespan track. Linear T5 HO (high output) lamps powered by efficient quick-start electronic ballasts deliver 10%-20% greater efficacy than comparable T8 fixtures.

### Benefits

- Fixture can be cable suspended or track mounted
- Available in 1 or 2 lamp configurations in 2', 3', or 4' lengths
- Versatile mounting options result in a fixture that can be used for wall washing, flood lighting, direct and indirect downlighting

### Features

- Integral louver for superior cut-off and glare control
- 180° to 360° of rotation for flexible aiming depending on mounting type
- Built-in pull-out lamp holder that allows for fast, easy re-lamping

### Application

- Fashion
- Food and Large Retailers

## PowerWash Track Heads

### Versions

