



R6 – versatility and accessibility

R6 Bollard

The R6 aluminum bollard is a versatile bollard luminaire ideal for commercial applications. It is available in incandescent, CFL, MH and HPS with wattages up to 100W. Also available with LED sources in warm and neutral CCT. Reflectors include Type V refractor bowl and a Type V specular aluminum internal cone with a stabilized, clear acrylic lens. A thermoset polyester powdercoat finish is electrostatically and available in three finishes plus an optional CraftStone™ finish. The RD6 luminaire features a 6" diameter body that's easy to lamp.

Benefits

- Up to 50,000 hour life
- Easy maintenance and relamping
- Prolonged component life

Features

- Available with a variety of lighting technologies
- Easy access to lamp
- Weatherproof ballast assembly

Application

- Walkway

R6 Bollard

Versions

