



# Refractive - blending classic beauty with modern technology in a versatile modular concept

## Refractive Post Top (R54)

The classic beauty of street lighting from the early 20th century is stylized in these post-top fixtures. The crisp clarity of acrylic, blended with today's modern technology, provides performance and style using the latest in prismatic refractor design and current lamp sources. The versatility of this design follows Hadco's renowned modular post top concept.

### Benefits

- Provides design flexibility
- Suitable for a variety of applications
- Quick and easy maintenance
- Easily retrofittable solution
- Fade and abrasion resistant

### Features

- Offers a variety of pod, roof and finial options
- Several reflector options available
- Able to meet Semi-Cutoff classification
- Compatible with LumiLock Retrofit LED Engine
- Polyester powdercoat finish
- Photocell option available

## Refractive Post Top (R54)

### Application

- Road and Street
- Bridges, Monuments, Facades

