



RLL1 - adding elegance and improved visibility to the low level environment

RLL1 Step Light

The low voltage RLL1 step light is a die-cast aluminum faceplate with galvanized steel, single gang recessed box with stainless steel fasteners and diecut neoprene gasket. Lamping specifications is a 12W maximum S-8 lamp with a frosted tempered glass lens.

Benefits

- Durable and lasting construction
- Quick and easy installation
- Fade and abrasion resistant

Features

- Die cast aluminum faceplate with galvanized steel
- Lamp included
- Low voltage quick connector included

Application

- Walkway

RLL1 Step Light

Versions

