



Going beyond the road

RoadView LED off road luminaire – medium (RVM)

Not all roadway applications are created equal. Poles that are mounted farther away from a roadway, multi-lane highways, toll plazas, and additional applications require special needs. Typical optics and mounting configurations will not meet these special requirements. The Lumec RoadView LED off road luminaire provides a solution to these unique applications. Combined with state-of-the-art optically efficient luminaires, the knuckle adapter can tackle even the most difficult installation. This flexible adapter can be mounted vertically or horizontally, based on existing or new pole configuration, for optimal performance.

Benefits

- Compatible with a full range of lighting control systems
- Up to 100,000 hour rated life
- Reduces amount of wasted light
- Easy to install and maintain
- Improved illuminance and uniformity

Features

- Versatile and expandable LED boards
- Highly efficient IP66 optics
- 3G vibration rated
- Tool-free access to electrical compartment
- 360 degree rotatable twist-lock photocell receptacle

Application

- Road and Street

RoadView LED off road luminaire - medium (RVM)

Versions

