



# RSCL2\_K5812 - the perfect solution for high pedestrian traffic and plant life applications

## RSCL2\_K5812 Steplight

The RSCL2\_K5812 is a low voltage step light with louver face plate made from die-cast aluminum back box that contains less than 0.3% copper to prevent corrosion in concrete or masonry applications. The finish is a thermoset polyester powdercoat is electrostatically applied. Optics include a UV stabilized, injection molded polycarbonate bubble faceplate, reinforced with frosted tempered glass along with a 24W maximum lamp.

### Benefits

- Superior durability
- UV and corrosion resistant
- Quick and easy installation

### Features

- Low copper aluminum construction
- Louvered optical assembly
- Lamp included
- Low voltage quick connector included

### Application

- Landscape
- Walkway

## RSCL2\_K5812 Steplight

### Versions

