



# RT/ST Strip – Improved lighting with energy savings

## RT/ST Recessed T8 Strip

The RT Recessed Strip provides improved lighting on merchandise or task area at reduced energy consumption when compared to other open strip systems.

### Benefits

- Designed to reduce energy consumption
- Recessed installation allows for cleaner, more comfortable appearance

### Features

- Available in your choice of reflectors: White baked enamel or specular aluminum
- Heavy-duty channel of code gauge die formed steel
- UL listed for damp locations

### Application

- Fashion
- Retail
- Office

## RT/ST Recessed T8 Strip

### Versions

